



TE360

IP20

3Ph Kwhmeter direct 100A with KNX output

Technical Features

Settings

Supported configuration mode	ETS
------------------------------	-----

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Architecture

Bus system	KNX
Type of pole	3P+N

Connectivity

With bus system Powernet	No
Type of connection	Direct connection

Electric current

Maximum measuring circuit current	100 A
-----------------------------------	-------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes