



TE360

IP20

3Ph Kwhmeter direct 100A with KNX output

Technical Features

Settings

Supported configuration mode ETS

Use conditions

Operating temperature -10 - 55 °C

Architecture

Bus system KNX

Type of pole 3P+N

Connectivity

With bus system Powernet No

Type of connection Direct connection

Electric current

Maximum measuring circuit current 100 A

Sustainability

REACH-SVHC free Yes

RoHS conform Yes