



VS112PF

Small distributor,golf,surface,1row,IP40,12M,MS-terminal,PE,white door

**Technical Features**

**Voltage**

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Equipment**

|                            |    |
|----------------------------|----|
| Number of rails            | 1  |
| Number of rows             | 1  |
| Number of section in width | 1  |
| With lock                  | No |
| Has neutral terminal block | No |

**Capacity**

|                   |    |
|-------------------|----|
| Number of modules | 12 |
|-------------------|----|

**Functions**

|                            |     |
|----------------------------|-----|
| Has protection main switch | No  |
| With conduit inlets        | Yes |

**Scope of delivery**

|                             |   |
|-----------------------------|---|
| Number of RCCB in enclosure | 0 |
|-----------------------------|---|

**Dimensions**

|        |        |
|--------|--------|
| Height | 252 mm |
| Width  | 282 mm |
| Depth  | 99 mm  |

**Cover, door**

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks         | 0 |

**Dimensions**

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

**Cover, door**

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

**Materials**

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

**Equipment**

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

**Materials**

|                       |    |
|-----------------------|----|
| Ultraviolet-resistant | No |
|-----------------------|----|

**Safety**

|                               |                              |
|-------------------------------|------------------------------|
| Protection class              | Isolation class II           |
| Impact resistance IK          | IK07                         |
| Ingress Protection (IP) class | IP40                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 650 °C                       |

---

**Sustainability**

---

RoHS conform

Yes