



47231404

**SCHUKO soc. out., enhncd contact prot., B.7, al., matt, lacq.**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Aluminium  
RAL code 9006  
Surface finish Matt  
Material Thermoplastic  
Treatment Untreated  
Varnished

**Dimensions**

Height 71 mm  
Width 71 mm  
Number of units 1  
Built-in depth flush-mounted boxes 31 mm  
Built-in depth 32 mm

**Connection**

Connector/plug type Plug-in terminal

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Plug-in connection  
Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO  
Rotated central insert No  
With hinged lid No  
With round protective earth pin No  
With signal lamp No  
With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection Yes  
Impact resistance IK IK05  
Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No  
With function lighting No

**Identification**

With imprint No

---

**Texts**

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

---

**Suitable for**

S.x/B.x

---

**Sustainability**

RoHS conform	Yes
--------------	-----