



47231404

SCHUKO soc. out., enhncd contact prot., B.7, al., matt, lacq.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Aluminium
RAL code 9006
Surface finish Matt
Material Thermoplastic
Treatment Untreated
Varnished

Dimensions

Height 71 mm
Width 71 mm
Number of units 1
Built-in depth flush-mounted boxes 31 mm
Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid No
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes
Impact resistance IK IK05
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

S.x/B.x

Sustainability

RoHS conform	Yes
--------------	-----