



WRDP50VNBSB

50A Double Pole Switch 2 Gang with LED Indicator Brushed Steel Black Insert

Technical Features

Installation, mounting

Mounting on Flush mounting

Materials

Colour Stainless steel

Surface finish Matt

Material Stainless steel

Treatment Brushed

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 20.20 mm

Electric current

Rated current 50 A

Texts

Lighting With control LED for ON

Push button No

Imprint With clear terminal markings

Sustainability

RoHS conform Yes