




WXD013D

Rocker for switch gallery 0-1 marking with light 2 modules dune

Technical Features

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Controls and indicators

Number of buttons	1
-------------------	---

Materials

Colour	White
RAL code	1013
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Height	44.60 mm
Depth	8 mm

Capacity

Number of modules	2
-------------------	---

Connectivity

Mounting type	Click mounting
---------------	----------------

Equipment

Monitoring window/light outlet	Yes
--------------------------------	-----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

Use conditions

Operating temperature	-10 - 35 °C
-----------------------	-------------

Texts

Imprint	Without imprint
---------	-----------------

Suitable for

gallery	
---------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes