



16417116

Relay switch centre plate for hotel card, K.1, ant., matt

Technical Features

Electric current

| | |
|---------------------------|------|
| Switching current | 10 A |
| Momentary contact current | 10 A |

Voltage

| | |
|---------------|-------|
| Rated voltage | 230 V |
|---------------|-------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Architecture

| | |
|---------------------------|------------|
| Control/operation element | Hotel card |
| Number of poles | 1 |

Power

| | |
|-------------------------------------|--------|
| 230 V incandescent and halogen lamp | 1500 W |
| Fluorescent lamps in duo circuit | 1500 W |

Materials

| | |
|----------------|------------------|
| Colour | Anthracite |
| Surface finish | Matt |
| Material | Metal Plastic |
| Treatment | Varnished |
| Transparent | No |

Dimensions

| | |
|------------------------------------|----------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 58.60 mm |
| Built-in depth | 32 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Controls and indicators

| | |
|------------------------------|----|
| With feedback signal contact | No |
|------------------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 50 °C |
|-----------------------|------------|

Texts

| | |
|--------------------|------------------------------|
| Imprint | With imprint "Hotelcard" |
| Installation mode | With spreader claws |
| Lighting | For illumination |
| Switch mode | 1-pole |
| Type of connection | With screw-in lift terminals |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|