



WGMCH2AS

**2G multi-gang frame (horizontal);as**

**Technical Features**

**Capacity**

Number of gangs	2
Number of modules	0

**Materials**

Colour	Aurora silver
Surface finish	Matt
Material	Polycarbonate (PC)
Contains recycled material (% of total plastic weight)	0 %
Treatment	Coated

**Dimensions**

Height	8 mm
Width	86 mm
Depth	8 mm

**Accessories**

Has labelling field	No
---------------------	----

**Installation, mounting**

Mounting on	Mounting plate
Mounting-/Connection Position	Front

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

**Use conditions**

Operating temperature	-20 - 45 °C
-----------------------	-------------

**Sustainability**

RoHS conform	Yes
--------------	-----