



WNA682B

**IP55**

**cubyko Double horizontal box empty with 2 sliders white IP55**

**Technical Features**

**Capacity**

Number of modules 2

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Contains recycled material (% of total plastic weight)	0 %
Treatment	Untreated

**Dimensions**

Number of units	2
Height	76 mm
Width	147 mm
Depth	56 mm
Built-in depth	65 mm

**Equipment**

With cable entry Yes

**Installation, mounting**

Mounting-/Connection Position	Horizontal
Mounting on	Surface mounting

**Accessories**

With frame cover Yes

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

**Use conditions**

Operating temperature -15 - 30 °C

**Safety**

Usable in higher IP class IP55 with closed cover

**Texts**

Installation mode	For horizontal mounting
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

**Suitable for**

cubyko  
cubyko

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes