




DBP245650ELN

Installation column floor, double sided, height 0.65m, Clip45, anodized

Technical Features

Dimensions

Depth	130 mm
Width	65 mm
Installation height	0.65 - 0.65 m
Height adjustment	0 mm
Inner cross-section	4400 - 4400 mm ²
Pole shape	Rectangular
Lid width	45 mm

Cover, door

Number of mountable lids	2
--------------------------	---

Equipment

Adjustable	No
Is portable	No

Cable

Cable entry position	Bottom
----------------------	--------

Installation, mounting

Ceiling mounting possible	No
Suitable for ground mounting	Yes

Materials

Material	Aluminium
Treatment	Anodised
Colour	Aluminium

Configuration

Number of sides for installation	Double side
----------------------------------	-------------

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

