



HIB416M

**Motorized transfer switch 4P 160A**

**Technical Features**

**Voltage**

Rated operational voltage  $U_e$  380 - 415 V

**Electric current**

Rated current 160 A

Rated conditional short-circuit current  $I_{cc}$  with gl-gG fuses 100 kA

**Power**

Rated operational power under 400 V AC AC1 105000 W

**Architecture**

Number of poles 4

Device construction type Fixed built-in

**Compatibility**

Suitable for DIN Rail No

Suitable for distribution board Yes

**Installation, mounting**

Mounting on Mounting plate