



2040



Mechanical timer, 15 min, light control

Technical Features

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Electric current

Switching current	16 A
Rated current	16 A

Functions

Runtime	15 min
---------	--------

Texts

Switch mode	2-pole off
Type of connection	With screw terminals
Terminal	With through terminal
Installation mode	Without spreader claws

Dimensions

Built-in depth	32.30 mm
----------------	----------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes