



WPPS12R



10AX Push Switch & Back Box without Knockouts

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Number of poles	2
-----------------	---

Materials

Colour	Grey
Surface finish	Glossy
Material	Metal
Treatment	Epoxy
Transparent	No

Dimensions

Height	86 mm
Width	86 mm
Depth	53.20 mm

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
Installation mode	For wall mounting
Switch mode	NO contact

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes