



WPPS12R



10AX Push Switch & Back Box without Knockouts

Technical Features

Electric current	
Momentary contact current	10 A
Voltage	
Rated voltage	250 V
Architecture	
Number of poles	2
Materials	
Colour	Grey
Surface finish	Glossy
Material	Metal
Treatment	Epoxy
Transparent	No
Dimensions	
Height	86 mm
Width	86 mm
Depth	53.20 mm
Installation, mounting	
Mounting on	Surface mounting
Controls and indicators	
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No
Connectivity	
Type of connection	Screw terminal
Safety	
Ingress Protection (IP) class	IP20
Accessories	
Has labelling field	No
Texts	
Imprint	Without imprint
Installation mode	For wall mounting
Switch mode	NO contact
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes