



80960271



IP20

Cover for 1gang for push-button module, clearlens, K.5, al., matt, lacq.

#### Technical Features

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

##### Materials

|                |               |
|----------------|---------------|
| Colour         | Aluminium     |
| RAL code       | 9006          |
| Surface finish | Matt          |
| Material       | Thermoplastic |
| Treatment      | Varnished     |

##### Dimensions

|        |       |
|--------|-------|
| Height | 55 mm |
| Width  | 70 mm |
| Depth  | 10 mm |

##### Settings

|                              |             |
|------------------------------|-------------|
| Supported configuration mode | ETS<br>easy |
|------------------------------|-------------|

##### Connectivity

|                           |                |
|---------------------------|----------------|
| With bus system KNX radio | No             |
| Mounting type             | Clamp mounting |

##### Equipment

|                                |     |
|--------------------------------|-----|
| Monitoring window/light outlet | Yes |
|--------------------------------|-----|

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

##### Texts

|         |                 |
|---------|-----------------|
| Imprint | Without imprint |
|---------|-----------------|

##### Suitable for

|     |  |
|-----|--|
| K.x |  |
|-----|--|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |