



80960275



IP20

**Cover for 1gang for push-button module, clearlens, K.1, ant., matt**

**Technical Features**

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

**Materials**

|                |               |
|----------------|---------------|
| Colour         | Anthracite    |
| RAL code       | 7021          |
| Surface finish | Matt          |
| Material       | Thermoplastic |
| Treatment      | Untreated     |

**Dimensions**

|        |       |
|--------|-------|
| Height | 55 mm |
| Width  | 70 mm |
| Depth  | 10 mm |

**Settings**

|                              |             |
|------------------------------|-------------|
| Supported configuration mode | ETS<br>easy |
|------------------------------|-------------|

**Connectivity**

|                           |                |
|---------------------------|----------------|
| With bus system KNX radio | No             |
| Mounting type             | Clamp mounting |

**Equipment**

|                                |     |
|--------------------------------|-----|
| Monitoring window/light outlet | Yes |
|--------------------------------|-----|

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

**Texts**

|         |                 |
|---------|-----------------|
| Imprint | Without imprint |
|---------|-----------------|

**Suitable for**

|     |  |
|-----|--|
| K.x |  |
|-----|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |