



JKD1416TM\_ISO

**125A Power/Lighting Board 4/16 Way Pan Assemblies Modbus Comms**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Architecture**

Number of poles	3
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Capacity**

Number of modules	60
-------------------	----

**Electric current**

Rated current	125 A
---------------	-------

**Dimensions**

Depth	165.50 mm
Height	1400 mm
Width	465 mm
Thickness of sidewall	1 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	Yes

**Materials**

RAL code	7035
Colour	Light grey
Material	Steel

**Connection**

Number of accessible phases	3
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

With energy meter	Yes
Extension possible	Yes
With socket outlet	No

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Number of earth leakage switches 300 mA	0