



JKD1416TM\_ISO

### 125A Power/Lighting Board 4/16 Way Pan Assemblies Modbus Comms

#### Technical Features

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Architecture

Number of poles	3
-----------------	---

##### Functions

Has protection main switch	Yes
Overvoltage protection	No

##### Capacity

Number of modules	60
-------------------	----

##### Electric current

Rated current	125 A
---------------	-------

##### Dimensions

Depth	165.50 mm
Height	1400 mm
Width	465 mm
Thickness of sidewall	1 mm

##### Cover, door

Interlockable	No
Door/cover is transparent	Yes

##### Materials

RAL code	7035
Colour	Light grey
Material	Steel

##### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

##### Connection

Number of accessible phases	3
-----------------------------	---

##### Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

##### Equipment

With energy meter	Yes
Extension possible	Yes

##### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30