



6768813515



Soc.out. earth. pin+hinged cover surf.-mtd, enhncd contact prot., W.1, grey matt

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 50 Hz

Materials

Colour Grey
RAL code 7011
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Dimensions

Height 76 mm
Width 76 mm
Depth 63.10 mm
Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Surface mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid Yes
With round protective earth pin Yes
With signal lamp No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 1

Safety

With enhanced contact protection No
Impact resistance IK IK05
Ingress Protection (IP) class IP55

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

| | |
|--------------------|-------------------------------------|
| Cover | Complete housing |
| Protection | Without enhanced contact protection |
| Type of connection | With plug-in terminals |

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |