



3315321909



3 x Cinch/S-Video soc. out., S.1/B.3/B.7, p. white, matt, plastic

#### Technical Features

##### Connection

Connector/plug type	Cinch S-video
Number of connections	4

##### Frequency

Frequency video	160 MHz
Audio frequency	20 - 20 Hz

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Metal Plastic
Treatment	Untreated

##### Dimensions

Height	71 mm
Width	71 mm
Depth	38 mm
Built-in depth flush-mounted boxes	28 mm

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

Shielded	Yes
With dust cover	No

##### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

##### Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

##### Suitable for

S.x/B.x	
---------	--

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes