



LF300G

Cylindrical fuse-links for industrial applications 10x38mm gG 0.5A 500V AC 120kA

Technical Features

Fuse

Fuse characteristics	gG
Fuse size	10.3 x 38

Electric current

Rated current	0.50 A
---------------	--------

Power

Total power loss under I _N	1.43 W
---------------------------------------	--------

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	120 kA
---	--------

Voltage

Type voltage supply	AC
Nominal voltage	500 - 500 V

Architecture

Curve	C
-------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes