



TU406



6-channel remote control

Technical Features

Frequency

Frequency transmission	868 - 868 MHz
Radio transmission frequency	868.30 MHz

Voltage

Operating voltage	6 - 6 V
-------------------	---------

Functions

Max. radio transmission range outdoors	100 m
----------------------------------------	-------

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Controls and indicators

Number of buttons	6
-------------------	---

Safety

Ingress Protection (IP) class	IP30
-------------------------------	------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Materials

Colour	Polar white
--------	-------------

Dimensions

Height	133.6 mm
Width	50.2 mm
Depth	16 mm

Equipment

With battery	Yes
--------------	-----

Battery

Battery life	5 years
--------------	---------

Texts

Function	Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control Reset function (to factory setting)
----------	------------------------------------------------------------------------------------------------------------------------------

Sustainability

RoHS conform	Yes
--------------	-----