



LF420G

Industrial fuse-links 14x51 gG 20A

Technical Features

Fuse

| | |
|----------------------|---------|
| Fuse characteristics | gG |
| Fuse size | 14 x 51 |

Electric current

| | |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Power

| | |
|---------------------------------------|--------|
| Total power loss under I _N | 2.50 W |
|---------------------------------------|--------|

Main electrical attributes

| | |
|---|-------|
| Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1 | 80 kA |
|---|-------|

Voltage

| | |
|---------------------|-------------|
| Type voltage supply | AC |
| Nominal voltage | 690 - 690 V |

Architecture

| | |
|-------|---|
| Curve | C |
|-------|---|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |