



LF432G

Industrial fuse-links 14x51 gG 32A

Technical Features

Fuse

Fuse characteristics	gG
Fuse size	14 x 51

Electric current

Rated current	32 A
---------------	------

Power

Total power loss under I <sub>N</sub>	3,50 W
---------------------------------------	--------

Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	120 kA
---	--------

Voltage

Type voltage supply	AC
Nominal voltage	500 - 500 V

Architecture

Curve	C
-------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes