




IP55 Motion Detector Comfort 220/360° White

EE870



Technical Features

Detection

Detection angle	220 - 360
Type of sensor	Movement detector

Settings

Time delay	5 S - 30 Min
------------	--------------

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Width	91 mm
Built-in depth	0 mm
Recommended installation height	2.50 - 2.50 m

Use conditions

Operating temperature	-20 - 55 °C
-----------------------	-------------

Materials

Colour	White
Material	Plastic

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Texts

Function	Presence simulation Can be used as a single unit, main device or extension unit
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes