




EE870



Motion detector comfort 220/360°, IP55, wall mounted, white

Technical Features

Detection

| | |
|-----------------|-------------------|
| Detection angle | 220 - 220 |
| Type of sensor | Movement detector |

Settings

| | |
|------------|--------------|
| Time delay | 5 S - 30 Min |
|------------|--------------|

Lighting

| | |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Dimensions

| | |
|---------------------------------|---------------|
| Width | 91 mm |
| Recommended installation height | 2.50 - 2.50 m |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20 - 55 °C |
|-----------------------|-------------|

Materials

| | |
|----------|---------|
| Colour | White |
| Material | Plastic |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP55 |
|-------------------------------|------|

Installation, mounting

| | |
|----------------------------|------------------|
| Mounting on | Surface mounting |
| Suitable for outdoor usage | Yes |

Texts

| | |
|--------------------|--|
| Function | Presence simulation Can be used as a single unit, main device or extension unit |
| Type of connection | With screw terminals |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |