



LF520G

Cylindrical fuse-links for industrial applications 22x58mm gG 20A 690V AC 120kA

Technical Features

Fuse

Fuse characteristics	gG
Fuse size	22 x 58

Electric current

Rated current	20 A
---------------	------

Power

Total power loss under IN	2.70 W
---------------------------	--------

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	80 kA
---	-------

Voltage

Type voltage supply	AC
Nominal voltage	690 - 690 V

Architecture

Curve	C
-------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes