



LF301G

Cylindrical fuse-links for industrial applications 10x38mm gG 1A 500V AC 120kA

**Technical Features**

**Fuse**

Fuse characteristics	gG
Fuse size	10.3 x 38

**Electric current**

Rated current	1 A
---------------	-----

**Power**

Total power loss under IN	2.77 W
---------------------------	--------

**Main electrical attributes**

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

**Voltage**

Type voltage supply	AC
Nominal voltage	500 - 500 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes