



LF332G

Cylindrical fuse-links for industrial applications 10x38mm gG 32A 400V AC 120kA

**Technical Features**

**Fuse**

Fuse characteristics	gG
Fuse size	10.3 x 38

**Electric current**

Rated current	32 A
---------------	------

**Power**

Total power loss under I <sub>N</sub>	2.90 W
---------------------------------------	--------

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	120 kA
-----------------------------------------------------------------------------------	--------

**Voltage**

Type voltage supply	AC
Nominal voltage	400 - 400 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes