



48046086

SCHUKO socket outlet/USB A-C Q.x, anthracite velvety, lacquered

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Output current	3000 mA
Rated current	16 A

Voltage

Output voltage	4.75 - 5.25 V
----------------	---------------

Use conditions

Operating temperature	5 - 35 °C
-----------------------	-----------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Output power	15 W
Power consumption standby	0.05 W

Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	45 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm
Built-in depth	32 mm

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting
Connector/plug type USB	AC

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Fuse	Short-circuit and overload-proof (electronic fuse)
Cover	Central cover plate
Connectors jacks	With USB socket type A + type C
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes