



LF440G

Industrial fuse-links 14x51 gG 40A

Technical Features

Fuse

Fuse characteristics	gG
Fuse size	14 x 51

Electric current

Rated current	40 A
---------------	------

Power

Total power loss under I _N	4.75 W
---------------------------------------	--------

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	120 kA
---	--------

Voltage

Type voltage supply	AC
Nominal voltage	500 - 500 V

Architecture

Curve	C
-------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes