



MM511N

Motor protection circuit breaker 3P 10-16A ; 4/7.5 kW at 230/415V

Technical Features

Electric current

Rated current	16 A
---------------	------

Dimensions

Height	140 mm
Width	45 mm
Depth	75 mm

Architecture

Control/operation element	Short rotary handle
Number of poles	3

Voltage

Rated impulse withstand voltage Uimp	6000 V
Overvoltage category according to IEC 60947-1	3
Type voltage supply	AC

Connectivity

Connection type control and aux contact	Screw terminal
---	----------------

Equipment

Sealable	No
With auxiliary contact	No
With thermal protection	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Sustainability

REACH conform	Yes
RoHS conform	Yes

Illustrations | Drawings

