



LSN403

Fuse carrier 3P 25A 400V L32 3M

Technical Features

Dimensions

Height	76.50 mm
Width	52.50 mm
Depth	76.90 mm

Architecture

Number of poles	3
-----------------	---

Electric current

Rated current	25 A
Rated current of fuse cartridge	2 A
	4 A
	6 A
	8 A
	10 A
	12 A
	16 A
	20 A
	25 A

Capacity

Number of modules	3
-------------------	---

Use conditions

Operating temperature	-40 - 70 °C
-----------------------	-------------

Installation, mounting

Nominal tightening torque	2.20 - 2.20 Nm
Mounting on	DIN rail

Power

Total power loss under IN	2.90 W
---------------------------	--------

Voltage

Rated insulation voltage U_i	690 V
Rated impulse withstand voltage U_{imp}	6000 V
Type voltage supply	AC
Overvoltage category according to IEC 60947-1	4

Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

Connection

Cross-section of input and output with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	1 - 16 mm ²

Fuse

Fuse size	8.5 x 31.5
-----------	------------

Cover, door

Interlockable	Yes
---------------	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes