



TKC110



Power supply with adapters for Coviva smartbox TKP100A

Technical Features

Electric current	
Output current	3000 mA
Intensity output 1	3 A
Functions	
Output voltage adjusted	Yes
Frequency	
Frequency	50 - 50 Hz
Capacity	
Number of modules	0
Voltage	
Output voltage	5 - 5 V
Use conditions	
Operating temperature	0 - 45 °C
Connectivity	
Type of connection	Plug-in connection
Dimensions	
Height	33.25 mm
Sustainability	
RoHS conform	Yes