




EE860



Motion detector comfort 220°, IP55, wall mounted, blanc

Technical Features

Detection	
Detection angle	220 - 220
Type of sensor	Movement detector

Settings	
Time delay	5 S - 30 Min

Lighting	
Response brightness adjustable	5 - 1000 lx

Frequency	
Frequency	50 - 60 Hz

Dimensions	
Width	91 mm
Recommended installation height	2.50 - 2.50 m

Use conditions	
Operating temperature	-20 - 55 °C

Materials	
Colour	White
Material	Plastic

Safety	
Ingress Protection (IP) class	IP55

Installation, mounting	
Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Texts	
Function	Presence simulation Can be used as a single unit, main device or extension unit
Installation mode	For wall and ceiling mounting, corner installation with adapter
Type of connection	With screw terminals

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes