



TU404



**4-channel remote control**

**Technical Features**

**Frequency**

Frequency transmission	868 - 868 MHz
Radio transmission frequency	868.30 MHz

**Voltage**

Operating voltage	6 - 6 V
-------------------	---------

**Functions**

Max. radio transmission range outdoors	100 m
--	-------

**Connectivity**

Radio protocol	KNX Radio
Receiver category	2

**Controls and indicators**

Number of buttons	4
-------------------	---

**Safety**

Ingress Protection (IP) class	IP50
-------------------------------	------

**Use conditions**

Operating temperature	-10 - 45 °C
-----------------------	-------------

**Dimensions**

Height	83 mm
Width	46.5 mm
Depth	15.80 mm

**Equipment**

With battery	Yes
--------------	-----

**Battery**

Battery life	5 years
--------------	---------

**Texts**

Function	Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control Reset function (to factory setting)
----------	--

**Sustainability**

RoHS conform	Yes
--------------	-----