



LF402G

Industrial fuse-links 14x51 gG 2A

Technical Features

Fuse

Fuse characteristics	gG
Fuse size	14 x 51

Electric current

Rated current	2 A
---------------	-----

Power

Total power loss under I _N	0.90 W
---------------------------------------	--------

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	80 kA
---	-------

Voltage

Type voltage supply	AC
Nominal voltage	690 - 690 V

Architecture

Curve	C
-------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes