



6765777103



Soc.out. earth.pin+hinged cover,enhncd contact prot.,screw-in lift ,K5 anodised

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Aluminium
RAL code 9006
Surface finish Matt
Material Aluminium
Treatment Anodised

Dimensions

Height 71 mm
Width 71 mm
Number of units 1
Built-in depth flush-mounted boxes 35 mm
Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet Earthing pin
Rotated central insert No
With hinged lid Yes
With round protective earth pin Yes
With signal lamp No
With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Hinged cover falls back, can be arrested in end position

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes
Impact resistance IK IK07
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting No

Texts

Imprint	With imprint
Cover	Central cover plate
Type of connection	With screw-in lift terminals

Suitable for

K.x

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes