



LF308PV

PV Fuse-link 10x38 mm 1000V DC 8A

Technical Features

Fuse

| | |
|----------------------|-----------|
| Fuse characteristics | gPV |
| Fuse size | 10.3 x 38 |

Electric current

| | |
|---------------|-----|
| Rated current | 8 A |
|---------------|-----|

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 2.55 W |
|---------------------------|--------|

Main electrical attributes

| | |
|---|-------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 30 kA |
|---|-------|

Voltage

| | |
|---------------------|---------------|
| Type voltage supply | DC |
| Nominal voltage | 1000 - 1000 V |

Architecture

| | |
|-------|---|
| Curve | C |
|-------|---|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |