



LF303PV

PV Fuse-link 10x38 mm 1000V DC 3A

Technical Features

Fuse

|                      |           |
|----------------------|-----------|
| Fuse characteristics | gPV       |
| Fuse size            | 10.3 x 38 |

Electric current

|               |     |
|---------------|-----|
| Rated current | 3 A |
|---------------|-----|

Power

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 1.35 W |
|---------------------------------------|--------|

Main electrical attributes

|   |       |
|---|-------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 30 kA |
|---|-------|

Voltage

|                     |               |
|---------------------|---------------|
| Type voltage supply | DC            |
| Nominal voltage     | 1000 - 1000 V |

Architecture

|       |   |
|-------|---|
| Curve | C |
|-------|---|

Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |