



TX510



**Presence detector 360° KNX, 2 channels, with BCU**

**Technical Features**

**Dimensions**

Installation height	4 - 4 m
Recommended installation height	2.5 - 3.5 m

**Settings**

Supported configuration mode	ETS easy
Minimal duty cycle	30 s

**Functions**

Maximal duty cycle	60 min
--------------------	--------

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Voltage**

Operating voltage over bus	21 - 32 V
----------------------------	-----------

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Electric current**

Bus current consumption data transfer	12 mA
---------------------------------------	-------

**Detection**

Detection angle	360 - 360
Detection angle horizontal	360 - 360

**Use conditions**

Operating temperature	0 - 45 °C
-----------------------	-----------

**Materials**

Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC)
----------	---

**Texts**

Function	Switching functions, dimming functions, blind control functions, value transmitter functions, forced control functions, scene functions, heating functions and timer functions, 2 channel mode
Installation mode	For ceiling mounting in 60 surface-mounted or hollow-wall box

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes