



TX510



Presence detector 360° KNX, 2 channels, with BCU

Technical Features

Dimensions

Installation height	4 - 4 m
Recommended installation height	2.5 - 3.5 m

Settings

Supported configuration mode	ETS easy
Minimal duty cycle	30 s

Functions

Maximal duty cycle	60 min
--------------------	--------

Connectivity

With bus system KNX radio	No
---------------------------	----

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Electric current

Bus current consumption data transfer	12 mA
---------------------------------------	-------

Detection

Detection angle	360 - 360
Detection angle horizontal	360 - 360

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Materials

Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC)
----------	---

Texts

Function	Switching functions, dimming functions, blind control functions, value transmitter functions, forced control functions, scene functions, heating functions and timer functions, 2 channel mode
Installation mode	For ceiling mounting in 60 surface-mounted or hollow-wall box

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes