



LF302PV

**PV Fuse-link 10x38 mm 1000V DC 2A**

**Technical Features**

**Fuse**

Fuse characteristics	gPV
Fuse size	10.3 x 38

**Electric current**

Rated current	2 A
---------------	-----

**Power**

Total power loss under I <sub>N</sub>	1.54 W
---------------------------------------	--------

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	30 kA
---	-------

**Voltage**

Type voltage supply	DC
Nominal voltage	1000 - 1000 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes