



TXA116



Power supply 2x 30V DC KNX 640 mA

Technical Features

Capacity

Number of modules	4
-------------------	---

Connectivity

With bus system KNX radio	No
---------------------------	----

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Output voltage	28 - 32 V
----------------	-----------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
----------------------------------	----------------------------

Cross-section rigid conductor	0.75 - 2.5 mm ²
-------------------------------	----------------------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Texts

Fuse	With electronic short-circuit and overload protection
------	---

Junction	Protected earth conductor must be connected
----------	---

Type of connection	With quickconnect plug-in terminals
--------------------	-------------------------------------

Power supply

Supply voltage	230 V AC
----------------	----------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----