



MZ527N

Alarm contact for motor starter 2C

Technical Features

Electric current

Rated current	1 A
Rated current 230 V AC15	3.50 A

Connectivity

Type of connection	Screw terminal
Mounting type	DIN rail adapter

Capacity

Number of modules	0.50
-------------------	------

Connection

Type of contacts	2NO
Cross-section flexible conductor	2.5 mm ²
Cross-section rigid conductor	2.5 mm ²

Voltage

Rated insulation voltage U _i	690 V
Rated impulse withstand voltage U _{imp}	6000 V
Type voltage supply	AC

Frequency

Frequency	40 - 60 Hz
-----------	------------

Endurance

Number of mechanical operations	10000
---------------------------------	-------

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Endurance

Electric endurance in number of cycles	5000
--	------

Use conditions

Storage/transport temperature	-25 - 80 °C
-------------------------------	-------------

Power

Total power loss under I _N	0.20 W
---------------------------------------	--------

Dimensions

Width	9 mm
Depth	68 mm

Equipment

Number of INV contacts	0
Number of NC contacts	0

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Illustrations | Drawings

