



ST320



**Safety transformer 18VA 230-12V**

**Technical Features**

**Voltage**

Output voltage	12 - 12 V
Rated operational voltage U <sub>e</sub>	230 - 230 V
Rated insulation voltage U <sub>i</sub>	4000 V

**Power**

Power consumption VA	18 VA
----------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Use conditions**

Operating temperature	-20 - 35 °C
-----------------------	-------------

**Capacity**

Number of modules	2
-------------------	---

**Dimensions**

Height	85 mm
Width	35 mm
Depth	58 mm

**Safety**

Ingress Protection (IP) class	IP20
Temperature protection	Yes

**Equipment**

Is short-circuit protected	Yes
On/off switch	No

**Connection**

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes