



EE610



IP55



LED deco lamp with IR detector, white

Technical Features

Dimensions

Installation height 4 - 4 m

Detection

Type of sensor Movement detector

Detection diameter on floor 12 - 12 m

Detection angle 140 - 140

Materials

Colour White

Material Acrylonitrile-Butadiene-Styrene (ABS)
Polycarbonate (PC)
Plastic

Reach distance

Max. transmission range frontally 12 m

Max. transmission range sideways 6 m

Voltage

Operating voltage 230 - 230 V

Lighting

Response brightness adjustable 5 - 1000 lx

Use conditions

Operating temperature -25 - 50 °C

Safety

Ingress Protection (IP) class IP55

Sustainability

REACH-SVHC free Yes

RoHS conform Yes