



LED deco lamp with IR detector, white

Technical Features

Dimensions

Installation height	4 - 4 m
---------------------	---------

Detection

Type of sensor	Movement detector
Detection diameter on floor	12 - 12 m
Detection angle	140 - 140

Materials

Colour	White
Material	Acrylonitrile-Butadiene-Styrene (ABS) Polycarbonate (PC) Plastic

Reach distance

Max. transmission range frontally	12 m
Max. transmission range sideways	6 m

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

Use conditions

Operating temperature	-25 - 50 °C
-----------------------	-------------

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes