



LF312PV

PV Fuse-link 10x38 mm 1000V DC 12A

Technical Features

Fuse

Fuse characteristics	gPV
Fuse size	10.3 x 38

Electric current

Rated current	12 A
---------------	------

Power

Total power loss under I <sub>N</sub>	2.60 W
---------------------------------------	--------

Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	30 kA
---	-------

Voltage

Type voltage supply	DC
Nominal voltage	1000 - 1000 V

Architecture

Curve	C
-------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes